

Please Fill Out Electronically (Complete only sections that apply / One datasheet per instrument unless instruments are identical)

Customer Data:

<b>Company:</b> _____	<b>Address:</b> _____
<b>Contact Person:</b> _____	<b>City/State/Zip:</b> _____
<b>Phone / Fax:</b> _____	<b>Email Address:</b> _____
<b>RA# / Service Order#</b> _____	

Type of Calibration:

**Type of Calibration:**

**Re-Zero instrument before start of calibration?** (E+H Standard = Yes, regarding Coriolis flow meters and gauge/diff pressure sensors)

**Number of Points:**

NOTE: E+H uses standard calibration values for standard calibrations. If custom points are required, please choose "Special" from the menu above and input the desired calibration points in the box below. Accredited calibrations will not be allowed if points requested are outside of our scope.

Calibration Points (use if special points are requested)

Cal Point #1:	Cal Point #2:	Cal Point #3:	Cal Point #4:	Cal Point #5:
---------------	---------------	---------------	---------------	---------------

**Calibration Location:**

**Regulated Industry?** Yes No

**Cal Stickers with "Due Date" Required?** Yes No If yes, please specify interval:

Instrument Data:

**Type of Instrument:** (select one only) For E+H instruments, only model# and serial# are needed.

Flow  Pressure  Temperature  Analysis / Other

Type:	Type: Application:	Type: (Class or Type) Immersion Length:	Type: If other,
-------	-----------------------	--	--------------------

**Input Voltage:** \_\_\_\_\_ **Output Type:** 4-20 mA Pulse/Freq Hart Profibus FF Other

**Accessories:** Local Indicator **Process connection type (NPT, Flange, Tri-clamp, etc.):** \_\_\_\_\_ **Line Size:** \_\_\_\_\_

**Manufacturer:** \_\_\_\_\_ **Model #:** \_\_\_\_\_ **Serial #:** \_\_\_\_\_ **Tag #:** \_\_\_\_\_

**On-site Data: (For on-site calibration only)**

Area Classification: Class \_\_\_\_\_ Div. \_\_\_\_\_ Gr. \_\_\_\_\_ Intrinsically Safe? Yes No Explosion-proof? Yes No

Sanitary Instrument? Yes No Loop Check required after calibration? Yes No MPE? (Maximum Permissible Error)

Environmental Conditions (at the calibration location): Temperature \_\_\_\_\_ Relative Humidity \_\_\_\_\_

NOTE: Onsite flow calibrations are performed on clean water only. All instruments being calibrated must be cleaned beforehand and will require a signed decontamination form. If MPE is not specified, then E+H will use a standard MPE value of 1, (% o.r., % o.f.s., or absolute, dependent on instrument type).

**Comments:**

NOTE: In order to provide an accurate calibration, it is necessary to have all components that are considered to be part of the instrument. Please ensure that the following items are included when removing instruments for calibration.

- Sensor (if separate from transmitter)
- Transmitter (if separate from sensor)
- Cabling (any interconnection cable from sensor to transmitter, i.e. non-integral/remote instruments)
- Manufacturer's Operation Manual (for non-E+H instruments)

**Reviewed by:** \_\_\_\_\_ **Date:** \_\_\_\_\_